

# Rx 100 *Interface Receiver*

*Addendum to manual for the following camera:*

**Mitsubishi CCD400E. (RS232 Controlled)**

**RX1\_M2V1**

## **Application Notes**

Manual zoom with 1 second slow inching

Manual focus override - returns to autofocus after holding focus key for 1 second

Iris override - returns to auto iris after holding iris key for 1 second

Cycle shutter speed

Cycle white balance options

Cycle backlight compensation - Set to 0 by holding iris key for 1 second

Reset camera to default settings

16 lens/camera setting presets

Advanced Features	Tx1000	Tx400DC	DM Mux
Shutter speed 1/50, 1/120, 1/250, 1/500, 1/1000, 1/2000, 1/4000, 1/10000	'#' WASH	'#' 1	*889 002
White Balance INDOOR, OUTDOOR, FL. LIGHT, LOCK, AUTO	'#' WIPE	'#' 2	*889 003
Backlight Compensation -30 - +30	'#' AUTOPAN	'#' 3	*889 004
Reset Camera settings 1/50, AUTO, AUTO IRIS, AUTO GAIN	'#' LIGHTS	'#' 4	*889 005

RS232 control of using the following connections:

Rx100	Description	Camera	9 pin DB Male
J3-C3	TxData-	RXD	Pin 3
J3-GND	Ground	SG	Pin 5

